

VIS-NIR Transmission Dip Probe

See More by [Ocean Optics](#)



Stock **#90-571** NEW [CONTACT US](#)

- 1 + **S\$1,874^{.60}**

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,874.60 each
Need More?	Request Quote

Product Downloads

SMA905

Fiber Connector Type:

General

TP300-VIS-NIR

Model Number:

Breakout 1.5 meter from end of the probe

Note:

VIS-NIR Transmission Dip Probe

Title:

Optical Properties	
400 - 2500	Wavelength Range (nm): (#90-570)
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Transmission Dip Probes Designed for Reliable In-Solution Absorbance/Transmission Measurements
- Rugged Stainless Steel or PEEK for Tough Process Conditions and Harsh Environments
- Flexible Path Lengths Available with Interchangeable Probe Tips
- Compatible with Ocean Optics Spectrometers and Accessories

Ocean Optics Transmission Dip Probes couple to spectrometers and light sources to measure absorbance and transmission in solutions. Choose from ruggedized high-pressure probe ([#90-569](#)) for demanding process environments or PEEK-jacketed probes ([#90-570](#) and [#90-571](#)) for harsh chemical conditions, spanning UV–VIS to VIS–NIR wavelengths. Easily customize your setup with accessories such as interchangeable probe tips in various path lengths and the protective sleeve ([#90-585](#)) for extended durability in corrosive or high-temperature applications. Ocean Optics Transmission Dip Probes are designed for seamless integration with [Ocean Optics spectroscopy systems and compatible accessories](#).