

[See all 5 Products in Family](#)

# Zinc Selenide, 25.4mm, Uncoated, IR Right Angle Prism

See More by [ISP Optics](#)



Infrared (IR) Right Angle Prisms

Stock **#64-123** **4 In Stock**

S\$2,184<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	S\$2,184.00 each
Qty 6-25	S\$1,750.00 each
Qty 26-49	S\$1,638.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Right Angle Prism **Type:**

**Physical & Mechanical Properties**

±0.25 **Dimensional Tolerance (mm):**

**Clear Aperture (%):**

85.00

35.90 **Length of Hypotenuse (mm):**

25.40 **Length of Legs (mm):**

### Optical Properties

Uncoated **Coating:**

Zinc Selenide (ZnSe) **Substrate:**

60-40 **Surface Quality:**

±10 **Angle Tolerance (arcmin):**

Left-Handed **Image Orientation:**

90 **Ray Deviation (°):**

600 - 18000 **Wavelength Range (nm):**

0.6 - 18 **Wavelength Range (µm):**

2λ **Surface Flatness (P-V):**

### Regulatory Compliance

**Compliant** **RoHS 2015:**

**Compliant** **Reach 224:**

**View** **Certificate of Conformance:**

## Product Details


Special care should be taken when handling Zinc Selenide as it is a toxic material. Always wear rubber or plastic gloves to avoid risk of contamination.


- CaF<sub>2</sub>, Ge, and ZnSe Substrates
- Ray Deviation of 90°
- Ideal for Use with Collimated Sources
- Additional [Infrared Optics](#) Available

ISP Optics Infrared (IR) Right Angle Prisms provide 90° or 180° redirection of laser beam or image paths depending on the input prism surface. Available with calcium fluoride (CaF<sub>2</sub>), germanium (Ge), or zinc selenide (ZnSe) substrates, these right-angle prisms are ideal for a range of IR laser and imaging applications. CaF<sub>2</sub> offer a low refractive index and broad transmission range from 0.2 – 7µm, making it useful for applications requiring high transmission from the UV through the IR. Ge is transmissive from 2 – 14µm with a high index of 4.002 at 11µm and is used in applications where the optical path length needs to be maximized. ZnSe has high, even transmission from 0.6 - 18µm and is typically integrated with CO<sub>2</sub> laser systems that feature a 632.8nm HeNe alignment laser and 10.6µm output beam. ISP Optics Infrared (IR) Right Angle Prisms can be used in combination for beam/image displacement.

**Note:** Special care should be taken when handling Zinc Selenide as it is a toxic material. Always wear rubber or plastic gloves to avoid risk of contamination.

## Technical Information






Right Angle Prism Ray Path



Right Angle Prism Ray Path



Right Angle Prism Tunnel Diagram



Right Angle Prism Tunnel Diagram

## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

