





SURFACE: IMA

IMA: 0.000 MM

SPOT DIAGRAM

32305
TUE DEC 16 2008 UNITS ARE μm .
FIELD : 1
RMS RADIUS : 1.097
GD RADIUS : 1.994
SCALE BAR : 4


REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

CHROMATIC FOCAL SHIFT

32305
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 89.2720 μm
DIFFRACTION LIMITED RANGE: 37.554 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM




TRANSVERSE RAY FAN PLOT

32305
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 50.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



POLYCHROMATIC DIFFRACTION MTF

32305
TUE DEC 16 2008
DATA FOR 0.4000 TO 0.7000 μm .
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM