





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	514.5 ± 2nm
FULL WIDTH HALF MAX (FWHM)	3 ± 2nm
MINIMUM TRANSMISSION	35%
BLOCKING	200 - 3500nm
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED RING
COATING TYPE	TRADITIONAL COATED

 **Edmund Optics®**



ALL DIMS IN

mm

TITLE

Ø25mm, 514.5nm x 3nm, BANDPASS FILTER

DWG NO

66610

SHEET  
1 OF 1