





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**




BANDPASS FILTER

	VALUE
OPTICAL DENSITY	≥ 4.0
CENTER WAVELENGTH (CWL)	$850 + 10.0 / - 0.0 \text{ nm}$
FULL WIDTH HALF MAX (FWHM)	$40 \pm 8 \text{ nm}$
MINIMUM TRANSMISSION	$> 50 \%$
BLOCKING	200 - Far IR
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED RING
COATING TYPE	TRADITIONAL COATED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



THIRD ANGLE PROJECTION 		TITLE	$\phi 25\text{mm}$, 850nm x 40nm, MOUNTED BANDPASS FILTER	
ALL DIMS IN	mm	DWG NO	67853	SHEET 1 OF 1