




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER



| | VALUE |
|--------------------------|---|
| CENTER WAVELENGTH (nm) | 445nm |
| FULL WIDTH HALF MAX (nm) | 10nm |
| MINIMUM TRANSMISSION | ≥85 |
| BLOCKING | 200 - 1200 |
| SURFACE QUALITY | 80-50 |
| CONSTRUCTION | MOUNTED IN BLACK ANODIZED ALUMINUM RING |
| COATING TYPE | HARD COATED |

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]



THIRD ANGLE
PROJECTION

ALL DIMS IN

mm

TITLE

OD4, Ø25mm, 445nm x 10nm, HC, BP FILTER

DWG NO

34500

SHEET
1 OF 1