

NOTES:




- 1. SUBSTRATE MATERIAL: Fused Silica
- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO 30 arcsec
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Enhanced Aluminum  
R(avg) >95% @ 450 - 650nm

S2: NONE

4. FINE GRIND SURFACE

5. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**Edmund Optics®**

REV. A	S1	S2	THIRD ANGLE PROJECTION				TITLE	5mm Square Enhanced Aluminum Coated, λ/10 Mirror	
SURFACE QUALITY	20-10	COMMERCIAL POLISH	ALL DIMS IN	mm	DWG NO	64008	SHEET 1 OF 1		
SURFACE FLATNESS	λ/10	NA							
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED							