

NOTES:

- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: RAVG ≤0.5% @ 600 - 1050nm



5. Rohs Compliant





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S 1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø9.00	Ø9.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

		Edmund Optics ®		
THIRD ANGLE _ PROJECTION	$\phi \Leftrightarrow$	TITLE	10mm DIA., 2mm THICK, NIR I COATED λ/4 N-BK7 WINDOW	
ALL DIMS IN	mm	DWG NO	83466	SHEET 1 OF 1