NOTES:

1. SUBSTRATE MATERIAL: FLOAT GLASS


2. ROHS COMPLIANT


3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 25% R ±5% @ 550nm 75% T ±5% @ 550nm

S2: NONE

EDGES CUT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

SHEET

1 OF 1

REV. A	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
SURFACE FLATNESS	4 - 6λ	4 - 6λ
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

		B	Control Edmund Optics®		
THIRD ANGLE PROJECTION	$\phi \Box$	TITLE	25 x 38mm, 25 R/75 T, PLATE BEAMSPLI	TTER	
ALL DIMS IN	mm	DWG NO	31437	SHEET 1 OF	