




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
CLEAR APERTURE	>90%	>90%
CENTER WAVELENGTH	$488 \pm 14.6\text{nm}$	$488 \pm 14.6\text{nm}$
FULL WIDTH HALF MAX (FWHM)	58.56nm	58.56nm
OPTICAL DENSITY	3 (abs)	3 (abs)
TRANSMISSION	>85%	>85%

**EO**<sup>®</sup> **Edmund Optics**<sup>®</sup>



ALL DIMS IN

mm

TITLE

488nm, 12.5mm Square, OD 3 Ultra-Thin  
Notch Filter

DWG NO

36330

SHEET  
1 OF 1