





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**




NOTCH FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
CLEAR APERTURE	>90%	>90%
CENTER WAVELENGTH	785 ±23.5nm	785 ±23.5nm
FULL WIDTH HALF MAX (FWHM)	62.8nm	62.8nm
OPTICAL DENSITY	3 (abs)	3 (abs)
TRANSMISSION	>85%	>85%

EO® **Edmund Optics**®

THIRD ANGLE
PROJECTION



TITLE

785nm, 12.5mm Dia., OD 3 Ultra-Thin Notch
Filter

ALL DIMS IN

mm

DWG NO

36398

SHEET
1 OF 1