



NOTES:



1. SUBSTRATE MATERIAL:
N-BK7
2. RoHS COMPLIANT
3. COATING (APPLY ACROSS COATING APERTURE)
S1: $R(ABS) \leq 1.5\%$ FROM 750-800nm @ 0° AOI
 $R(ABS) \leq 1.0\%$ FROM 800-1550nm @ 0° AOI
 $R(AVG) \leq 0.7\%$ FROM 750-1550nm @ 0° AOI
S2: NONE

 4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	 Edmund Optics®			
SHAPE	PLANO	PLANO				
ANGLE TOL.	±0°3'	±0°3'		TITLE	12.7mm NIR II 1/4 WAVE FRESNEL RHOMB RETARDER DWL 1064nm	
SURFACE QUALITY	20-10	20-10				
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	36142
					SHEET 1 OF 1	