



NOTES:

1. SUBSTRATE MATERIAL:
N-BK7
2. RoHS COMPLIANT
3. COATING (APPLY ACROSS COATING APERTURE)
S1: $R(ABS) \leq 1.5\%$ FROM 750-800nm @ 0° AOI
 $R(ABS) \leq 1.0\%$ FROM 800-1550nm @ 0° AOI
 $R(AVG) \leq 0.7\%$ FROM 750-1550nm @ 0° AOI
S2: NONE


 4. FINE GRIND SURFACE

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

REV. A	S1	S2	THIRD ANGLE PROJECTION 		TITLE	12.7mm NIR II 1/2 WAVE FRESNEL RHOMB RETARDER DWL 1064nm	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	20-10	20-10	ALL DIMS IN	mm	DWG NO	36148	SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					