



NOTES:


1. COATING:
S1: MaxiBlack™
THICKNESS (μm) 4 - 6
2. ABSORBANCE: 98%
3. ABRASION RESISTANCE: Moderate
4. HUMIDITY RESISTANCE: MIL-C-48497A
5. OPERATING TEMPERATURE: -50 to 150
6. WAVELENGTH RANGE: 0.3 - 5



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	MaxiBlack Low Outgassing Adhesive Polymer Film 200 x 300mm	
ALL DIMS IN	mm	DWG NO	13488	SHEET 1 OF 1