



NOTES:


1. COATING:  
S1: MaxiBlack™  
THICKNESS (μm) 4 - 6
2. ABSORBANCE: 98%
3. ABRASION RESISTANCE: Moderate
4. HUMIDITY RESISTANCE: MIL-C-48497A
5. OPERATING TEMPERATURE: -250 to 290
6. WAVELENGTH RANGE: 0.3 - 5



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO**® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	MaxiBlack No Adhesive Polymer Film 200 x 300mm	
ALL DIMS IN	mm	DWG NO	13492	SHEET 1 OF 1