



PART	PART #	MATERIAL
①	#32-759	SCHOTT RG850
②	#56-353	BLACK ANODIZED ALUMINUM



SECTION A-A

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

SHAPE	PLANO
SPECTRAL TRANSMITTANCE (%)	97
PASSBAND LIMIT 1 (nm)	120
CUT-OFF POSITION (nm)	850±9
STOPBAND LIMIT (nm)	700
WAVELENGTH	IR

THIRD ANGLE PROJECTION

ALL DIMS IN mm

 Edmund Optics®

TITLE

22mm CA, SCHOTT RG850, C-Mount
Longpass Glass Color Filter

DWG NO

13038

SHEET
1 OF 1