

NOTES:


- 1. SUBSTRATE: FUSED SILICA
- 2. S2 TO BE PARALLEL WITH S1 TO WITHIN < 1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) S1 & S2: R(AVG) \leq 1.5% FROM 250-700nm R(ABS) \leq 1.0% FROM 350-450nm

4. FINE GRIND SURFACE

5. Rohs Compliant







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE (mm)	Ø36.00	Ø36.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE _ PROJECTION	ϕ	TITLE
ALL DIMS IN	mm	DWG NO

Edmund Optics ®
40mm DIA., 4mm THICK, UV-VIS COATED, λ/4 FUSED SILICA WINDOW

MS IN mm DWG NO 14978 SHEET 1 OF 1