

## NOTES:

- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO < 1ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AVG) ≤1.75% @ 400 - 700nm

4. FINE GRIND SURFACE

5. Rohs Compliant





## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Ontion

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE (mm)	Ø45.72	Ø45.72
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

					S
	THIRD ANGLE _ PROJECTION		TITLE	50.8mm DIA., 4mm THICK, MgF2 COA λ/4 N-BK7 WINDOW	ATED
)	ALL DIMS IN	mm	DWG NO	15430	SHEET 1 OF