



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

NOTES:


1. SUBSTRATE: ISUZU ISK150
DENSITY: 2.58g/cm³
REFLECTION FACTOR: 0.92
KNOOP HARDNESS: 497kg/mm²
REFRACTIVE INDEX: 1.516nm
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 3 ARCMIN



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1
SHAPE	PLANO
FUNCTION	HEAT ABSORBING
SURFACE QUALITY	60-40
CLEAR APERTURE	$\varnothing 45.00$
BEVEL MAX FACE	PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION



ALL DIMS IN

mm

 **Edmund Optics®**

TITLE	ISUZU ISK150, 50 Dia., HEAT ABSORBING COLORED GLASS FILTER		
DWG NO	15711	SHEET	1 OF 1