




NOTES:
1. RoHS: COMPLIANT

2. DAMAGE THRESHOLD:
PULSED LIDT: 5.0 J/cm² * (τ/[ns])^{0.30}
CW LIDT: 5.0 MW/cm²


3. GROUP DELAY DISPERSION: 759 fs²



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE	160mm, 1030-1080nm JENar™ Silverline™ F-Theta Scanning Lens	
ALL DIMS IN	mm	DWG NO	16769	SHEET 1 OF 1