NOTES:


1. SUBSTRATE: Float Glass


2. COATING (APPLY ACROSS CLEAR APERTURE)

\$1: Dielectric, ±5% R/T @ 550nm \$2: AR 1/4 WAVE MgF2 @ 550nm



4. ROHS COMPLIANT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2			
SHAPE	PLANO	PLANO			
SURFACE QUALITY	80-50	80-50			
SURFACE FLATNESS	4 - 6λ	4 - 6λ			
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED			

		Edmund Optics ®			
THIRD ANGLE PROJECTION		TITLE	12.5 x 12.5mm, 25R/75T, AR Coated Plate Beamsplitter		
 ALL DIMS IN	mm	DWG NO	13396	SHEET 1 OF 1	