NOTES:


1. SUBSTRATE: Float Glass


2. COATING (APPLY ACROSS CLEAR APERTURE)

\$1: Dielectric, ±5% R/T @ 550nm \$2: AR 1/4 WAVE MgF2 @ 550nm



4. ROHS COMPLIANT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
SURFACE FLATNESS	4 - 6λ	4 - 6λ
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION		TITLE	12
ALL DIMS IN	mm	DWG NO	

12.5 x 12.5mm, 75R/25T, AR Coated Plate

Edmund Optics®

 S IN
 mm
 DWG NO
 13401
 SHEET 1 OF 1