
NOTES:


- 1. SUBSTRATE: Float Glass
- 2. COATING (APPLY ACROSS CLEAR APERTURE)

\$1: Dielectric, ±5% R/T @ 550nm \$2: AR 1/4 WAVE MgF2 @ 550nm



4. ROHS COMPLIANT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Ontion

	\$1	S2			
SHAPE	PLANO	PLANO			
SURFACE QUALITY	80-50	80-50			
SURFACE FLATNESS	4 - 6λ	4 - 6λ			
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED			

				B Edmund Optic	S
THIRD ANGLE PROJECTION		TITLE	25 x 25mm, 70R/30T, AR Coated Plate Beamsplitter		
	ALL DIMS IN	mm	DWG NO	13406	SHEET 1 OF 1