




NOTES:

- 1. SUBSTRATE:  
SCHOTT KG1
- 2. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1 & S2: NONE

3. FINE GRIND SURFACE

- 4. DENSITY (g/cm³) : 2.53  
OPERATING TEMPERTURE (°C): 300 Maximum  
REFLECTION FACTOR: 0.92
- 5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION		TITLE	SCHOTT KG1, 25mm Dia., 1mm Thick, Colored Glass Heat Absorbing Shortpass Filter	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	60-40	60-40	ALL DIMS IN	mm	DWG NO	19319	SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					