





- NOTES:
- 1. SUBSTRATE: Aluminum Wires on COP
 - 2. EXTINCTION RATIO: >1415:1 (@ 0° AOI, 550nm)
 - 3. TRANSMISSION (%): 84.9 (Typical @ 550nm)
 - 4. WAVELENGTH RANGE: 400 - 1200 nm
 - 5. ORIENTATION OF AXIS: 0° ± 1.5°
NOTCHES ON POLARIZING FILM DEPICT DIRECTION OF POLARIZATION DIRECTION
 - 6. RoHS3 COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE	25 x 25 mm Stabilized Wire Grid Polarizing Film	
ALL DIMS IN	mm	DWG NO	20235	SHEET 3 OF 6