NOTES:

1. SUBSTRATE:

N-BK7


- 2. S2 TO BE PARALLEL TO S1 TO <30 arcsec
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


S1 & S2: R(ABS) ≤0.25% @ 880nm R(AVG) ≤1.25% @ 400 - 870nm R(AVG) ≤1.25% @ 890 - 1000nm




FINE GRIND SURFACE

Rohs Compliant







DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2			
SHAPE	PLANO	PLANO			
SURFACE QUALITY	20-10	20-10			
WAVELENGTH RANGE	400 - 1000nm	400 - 1000nm			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			
	-	-			

			Edmund Optics			
	THIRD ANGLE PROJECTION		TITLE	20mm Diameter VIS-NIR Coated, Ultra-Thin N-BK7 Window		
D	ALL DIMS IN	mm	DWG NO	22039	SHEET 1 OF 1	