




- NOTES:
- 1. SUBSTRATE:
Tritan
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: NONE
S2: NONE
 - 3. CENTERING: ≤25 ARCMIN



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	34.00	 Edmund Optics®		
			BFL @ 587.6nm	18.10			
SHAPE	CONVEX	PLANO		TITLE	51.7mm Dia. x 34mm FL, Uncoated, Molded Condenser Lens with Smooth Diffuser		
SURFACE QUALITY	AS MOLDED	SMOOTH DIFFUSER					
CLEAR APERTURE	Ø 43.20	Ø 43.20					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	22686	SHEET 1 OF 1