

[See all 76 Products in Family](#)

# LightPath 354280 | 6.5mm Dia., 0.15 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-114** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ **S\$119<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-10	<b>S\$119.00</b> each
Qty 11-49	<b>S\$107.10</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Thickness: 0.25 (t) (mm)  
Material: BK7

**Compatible Window:**

354280

**Lightpath Lens Code:**

Aspheric Lens

**Type:**

Collimate or Focus Laser Light

Typical Applications:

## Physical & Mechanical Properties

6.50 ±0.020 Diameter (mm):

5.5 Clear Aperture CA (mm):

1.78 Edge Thickness ET (mm):

2.18 ±0.05 Center Thickness CT (mm):

Protective as needed Bevel:

15.856 Distance from Window to Lens (D) (mm):

## Optical Properties

18.40 @ 780nm Effective Focal Length EFL (mm):

0.15 Numerical Aperture NA:

D-ZK3 Substrate: □

±1 Focal Length Tolerance (%):

780 Aspheric Design Wavelength (nm):

BBAR (600-1050nm) Coating:

R<sub>abs</sub> <1.0% @ 600 - 1050nm Coating Specification:

40-20 Surface Quality:

3.33 f#:

60.88 Abbe Number (v<sub>d</sub>):

1.586 Index of Refraction (n<sub>d</sub>):

600 - 1050 Wavelength Range (nm):

17.11 Working Distance (mm):

Infinite Conjugate Distance:

780.00 Focal Length Specification Wavelength (nm):

< 0.09 Transmitted Wavefront Error (λ, RMS):

## Material Properties

7.6 Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):

## Environmental & Durability Factors

≤200 Operating Temperature (°C):

## Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 247:


## Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser



## Technical Information



## Compatible Mounts