

## 0.19 - 20 $\mu$ m, 110W, Thermopile Power & Energy Detector



0.19 - 20 $\mu$ m, 110W, Thermopile Power & Energy Detector

Stock **#78-465** **1 In Stock**

- 1 + **\$3,080<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1-4	<b>\$3,080.00</b> each
Qty 5+	<b>\$2,772.00</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

Maximum Incident Energy Density (J/cm<sup>2</sup>, 10ns Pulses):

1

### General

UP19k-100F-H9-INT-D0 (US) **Model Number:**

Fan Cooled **Cooling Method:**

Integra (Integrated) **Compatible Meters:**

## Physical & Mechanical Properties

54.2 x 54.2 x 55.6      **Dimensions (mm):**

160      **Weight (g):**

0.16      **Weight (kg):**

19      **Active Area (mm):**

## Optical Properties

190 - 20000      **Wavelength Range (nm):**

0.19 - 20      **Wavelength Range (µm):**

## Sensor

Thermopile      **Type of Sensor:**

## Electrical

110,000      **Maximum Incident Beam Power (mW):**

110      **Maximum Incident Beam Power (W):**

45,000      **Maximum Incident Power Density (W/cm<sup>2</sup>):**

45      **Maximum Incident Power Density (kW/cm<sup>2</sup>):**

3 mW      **Noise Level:**

## Regulatory Compliance

[View](#)      **Certificate of Conformance:**

## Product Details

- Photodetectors, Thermopiles, and Pyroelectric Detectors Available
- Various Active Area Sizes Across a Wide Range of Sensitivities
- [Meterless](#) and [Wireless](#) Detectors Also Available

Gentec-EO Integra USB Power and Energy Detectors combine a power meter and detector in one convenient package while providing fast response times and accurate measurements for beam analysis. These detectors are designed with a USB connector for easy connection to a PC or other acquisition system and include user-friendly software allowing for control via PC or serial commands. Versatile pyroelectric energy detectors with broadband coatings are optimized for low to high power densities. Gentec-EO Integra USB Power and Energy Detectors can be used with a variety of laser powers ranging from the nanowatts to multi-kilowatts. These detectors are ideal for laser energy measurement, thermal imaging, and remote sensing applications.