

[See all 76 Products in Family](#)

LightPath 354125 | 11mm Dia., 0.50 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#33-426** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ **S\$166⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-10	S\$166.60 each
Qty 11-49	S\$149.80 each
Need More?	Request Quote

Product Downloads

General

Thickness: 0.25 (t) (mm)
Material: B-K7

Compatible Window:

354125

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:
Collimate or Focus Laser Light

Physical & Mechanical Properties

Diameter (mm):
11.00 ±0.015

Clear Aperture CA (mm):
10

Edge Thickness ET (mm):
1.092

Center Thickness CT (mm):
3.64 ±0.40

Bevel:
Protective as needed

Optical Properties

Effective Focal Length EFL (mm):
10.00 @ 633nm

Numerical Aperture NA:
0.50

Substrate:
[D-ZK3](#)

Focal Length Tolerance (%):
±1

Aspheric Design Wavelength (nm):
633

Coating:
BBAR (600-1050nm)

Coating Specification:
 $R_{\text{abs}} < 1.0\%$ @ 600 - 1050nm

Surface Quality:
60-40

f#:
1.00

Abbe Number (v_d):
60.88

Index of Refraction (n_d):
1.586

Wavelength Range (nm):
600 - 1050

Working Distance (mm):
7.8

Conjugate Distance:
Infinite

Focal Length Specification Wavelength (nm):
633.00

Transmitted Wavefront Error (λ , RMS):
< 0.09

Material Properties

Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$):
7.6

Environmental & Durability Factors

Operating Temperature ($^{\circ}\text{C}$):
≤200

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.

Technical Information

