

TECHSPEC[®] 0.69X In-Line Illumination CobaltTL Telecentric Lens



Stock **#15-873** 6 In Stock

-

1

+

S\$3,992⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$3,992.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Series:

CobaltTL Series

Stock No. of Mounting Clamp:

[#63-233](#)- Sold Separately

Type:


Telecentric Lens

In-Line Illumination		Type of Illumination:
Physical & Mechanical Properties		
Variable	Iris Option:	
179.00	Length (mm):	
175.00	Length excluding Threads (mm):	
55	Maximum Diameter (mm):	
792.4	Weight (g):	
Optical Properties		
20.39mm	Horizontal Field of View, 1.1" Sensor:	
18.55mm	Horizontal Field of View, 1" Sensor:	
12.75mm	Horizontal Field of View, 2/3" Sensor:	
10.43mm	Horizontal Field of View, 1/1.8" Sensor:	
9.27mm	Horizontal Field of View, 1/2" Sensor:	
17.60	Maximum Image Circle (mm):	
0.058	Numerical Aperture NA, Object Side:	
9 (7)	Number of Elements (Groups):	
0.69X	Primary Magnification PMAG:	
0.69	Telecentric Lens Magnification:	
110	Working Distance (mm):	
20.4 x 15.3	FOV @ Max Sensor Format, H x V (mm):	
f/4.5 - f/22	Aperture (f/#):	
N/4 MgF ₂	Coating:	
±1.08mm at f/10 (20% @ 20 lp/mm)	Depth of Field (mm):	
0.69X	Magnification:	
<0.027	Typical Distortion @ 520nm (%):	
<0.086	Typical Telecentricity @ 520nm (°):	
VS	Lens Wavelength Range:	
Sensor		
1.1"	Maximum Sensor Format:	
2.20	Pixel Size (µm):	
Threading & Mounting		
M52 x 0.75 (Female)	Filter Thread:	
C-Mount	Mount:	
Regulatory Compliance		
View	Certificate of Conformance:	


- High Resolution Bi-Telecentric Lens with In-Line Illumination Options
- Up to 20 MegaPixels, 2.2µm Pixel Size
- 1.1", C-Mount Telecentric Lens with f/#s as Low as f/4

TECHSPEC® CobaltTL Telecentric Lenses are designed for semiconductor and electronics inspection, measurement, and gauging applications. These telecentric lenses achieve high light throughput with industry leading low f/#s. Featuring less than 0.015° telecentricity and low 0.013% distortion, these lenses are ideal for image stitching applications. These 17.6mm diagonal sensor format lenses are compatible with the Sony IMX304 1.1” sensors and other similar format sensors such as the Sony IMX183. TECHSPEC® CobaltTL Telecentric Lenses produce unparalleled levels of contrast yielding maximum image quality with the highest degree of measurement accuracy. In-line versions provide the ability to rotate/reposition the inline illumination port to allow for maximum flexibility when machine building. TECHSPEC® CobaltTL Telecentric Lenses are compatible with high vibration environments and feature a removable recessed set screw for securely locking the iris in place.


TECHNICAL INFORMATION




#15-873, 0.69X In-Line Illumination CobaltTL Telecentric Lens, Distortion Plot




#15-873, 0.69X In-Line Illumination CobaltTL Telecentric Lens, Relative Illumination Plot




#15-873, 0.69X In-Line Illumination CobaltTL Telecentric Lens, Telecentricity Plot




#15-873, 0.69X In-Line Illumination CobaltTL Telecentric Lens, Modulated Transfer Function (MTF) Plot, 110mm Working Distance, f6



#15-873, 0.69X In-Line Illumination CobaltTL Telecentric Lens, Depth of Field Plot, 110mm Working Distance, f6



#15-873, 0.69X In-Line Illumination CobaltTL Telecentric Lens, Modulated Transfer Function (MTF) Plot, 110mm Working Distance, f10



#15-873, 0.69X In-Line Illumination CobaltTL Telecentric Lens, Depth of Field Plot, 110mm Working Distance, f10



Description		Stock No.	Length (A)	Front Diameter (B)	Back Diameter (C)
0.28X	C-Mount	#62-921	197.59mm	138.6mm	50mm
0.36X	C-Mount	#88-602	163.5mm	70mm	43.5mm
0.5X	C-Mount	#62-911	172.9mm	90mm	50mm
0.55X	C-Mount	#88-603	182.5mm	62mm	43.5mm
0.69X	C-Mount	#15-872 / #15-873 (In-Line)	174.96mm	55mm	46mm
0.9X	C-Mount	#62-901	199.8mm	65mm	53mm
