

[See all 13 Products in Family](#)

Coherent® VHK™ Circular Beam Visible Laser Diode 0221-698-01 | 0.95mW 635nm

See More by [Coherent®](#)



Coherent® VHK™ Circular Beam Visible Laser Diode

Stock #54-023 **5 In Stock**

⊖ 1 ⊕ **\$791⁰⁰**

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | \$791.00 each |
| Need More? | Request Quote |

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

Diode **Type of Laser:**

II **Laser Class - CDRH:**

Physical & Mechanical Properties

<4 **Pointing Accuracy (mrad):**

0.580 Diameter (inches):

1.32 Length (inches):

Optical Properties

635.00 Wavelength (nm):

1.1 @ module face Beam Diameter (mm):

0.70 Beam Divergence (mrad):

Red Color:

Electrical

0.95 Output Power (mW):

70/200 (Typical/Maximum) Current (mA):

Hardware & Interface Connectivity

Power Supply:
Power Supply Required and Sold Separately.
USA: [#59-099](#)
Europe: [#35-201](#)
Japan: [#59-099](#)
Korea: [#33-771](#)
China: [#59-099](#)

5-10VDC Power Requirement:

red (+), black (-), case (+) Electrical Leads/ Pin Connections:

Free Space Output Type:

5-10 DC Input Voltage (V):

Environmental & Durability Factors

-10 to +40 Operating Temperature (°C):

-40 to +80 Storage Temperature (°C):

Regulatory Compliance

[Exempt](#) RoHS 2015:

[View](#) Certificate of Conformance:

Product Details

- Robust, High Quality Laser Diodes with Small Form Factor
- 635nm and 670nm High Visibility Wavelengths
- Sophisticated Electronic Design for Consistent Beam Properties

Coherent® Visible Laser Diode Modules feature a compact form factor to help users achieve space saving designs in systems that require a collimated light source. The simple design of these laser diodes allows for quick and efficient incorporation into a wide array of optical systems. A sophisticated electronic design aids in producing consistent laser power and beams. Coherent® Visible Laser Diode Modules with advanced AlignLock™ optical assembly technology provide a remarkable beam-pointing alignment of <4.3mrad, making these laser diodes a great choice for precision applications. These robust, compact laser diodes are typically used in machine vision, medical equipment, and many other industrial applications.

Note: [Power Supply](#), sold separately, is required for operation.

Technical Information



VLM™ High Quality Laser Diode Module - Micro Series



VLM™ High Quality Laser Diode Modules