

[See all 20 Products in Family](#)

TECHSPEC® 0° AOI, 20.0mm Square, Cold Mirror



TECHSPEC High Performance Cold Mirrors

Stock **#64-436** **4 In Stock**

⊖ 1 ⊕ **\$75⁰⁰**

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-9 | \$75.60 each |
| Qty 10-25 | \$67.90 each |
| Qty 26-49 | \$64.75 each |
| Need More? | Request Quote |

Product Downloads

General

Cold Mirror

Type:

Physical & Mechanical Properties

1.10 ±0.2

Thickness (mm):

20.0 x 20.0

Dimensions (mm):

Dimensional Tolerance (mm):

+0.0/-0.2

Length (mm):

20.00

Width (mm):

20.00

Optical Properties

Transmission (%):

Longpass Filter

Coating Type:

Dielectric

Coating:

Cold Mirror, 0°

Surface Flatness (P-V):

4 - 6λ

Wavelength Range (nm):

400 - 1150

Substrate:

BOROFLOAT®

Angle of Incidence (°):

0

Coating Specification:

R_{avg} ≥95% @400 - 690nm and T_{avg} ≥90% @750 - 1200nm
AR Coating: R_{avg} <1% @700 - 1150nm

Surface Quality:

80-50

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:



Compliant

Product Details

- >95% Reflection from 400 - 690nm
- >90% Transmission from 750 - 1200nm
- Optimized for 0° or 45° Angle of Incidence

TECHSPEC® High Performance Cold Mirrors feature a multi-layer dielectric coating optimized for greater than 95% reflection of visible light and greater than 90% transmission of IR wavelengths. Cold mirrors are designed for use in any application where heat build-up can cause damage or adverse effects. For high power illumination, forced air cooling is recommended.

Technical Information



Quote Your Size

Compatible Mounts

