

1030nm High Performance Laser Line Filter 25mm Dia.



High Performance Laser Line Bandpass Filters

Stock **#12-281** **1 In Stock**

☐ [Additional Bandwidths](#)

-

1

+

S\$1,192⁸⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,192.80 each
Need More?	Request Quote

Product Downloads

General

Type:

Bandpass Filter

Physical & Mechanical Properties

Diameter (mm):

25.00 +0.0/-0.1

Clear Aperture CA (mm):

≥22

Thickness Tolerance (mm):

±0.10

Mounted in Black Anodized Ring	Construction:
Physical Durability: ML-C-48497A Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, and 4.5.5.3	
2.0 ±0.1	Substrate Thickness (mm):

Optical Properties

0 ±2	Angle of Incidence (°):
3.9	Bandwidth (nm):
OD 5 Blocking Wavelength Range (nm) : 947.6 - 1014.6 & 1040.3 - 1368.2	
OD 6 Blocking Wavelength Range (nm): 1014.6 - 1019.7 & 1045.5 - 1133	
≥6.0	Optical Density OD (Average):
1,030.00	Center Wavelength CWL (nm):
1030	Design Wavelength DWL (nm):
3.90 - 7.2	Full Width-Half Max FWHM (nm):
Fused Silica	Substrate: ☐
>90	Minimum Transmission (%):
Hard Coated	Coating:
60-40	Surface Quality:
>90	Transmission (%):
Blocking Wavelength Range (nm): 947.6 - 1014.6 & 1040.3 - 1368.2	

Threading & Mounting

3.5 ±0.1	Mount Thickness (mm):
----------	-----------------------

Environmental & Durability Factors

ML-STD-810F Paragraphs 501.4, 502.4, and 507.4	Environmental Durability:
--	---------------------------

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:







Product Details

- Over 90% Transmission at Specified Laser Lines
- Hard Coated Design
- Designed for Laser Applications

Available for use with common gas and solid state lasers, High Performance Laser-Line Bandpass Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisy spontaneous emission. These laser line filters are available at popular diode and Nd:YAG laser lines, including 532nm, 785nm, and 1064nm. High Performance Laser-Line Bandpass Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, High Performance Laser-Line Bandpass Filters are excellent complements to TECHSPEC® Notch Filters and [Laser Line Longpass Filters](#).

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 0.1 J/cm² @ 532nm, 10ns.

Technical Information



Compatible Mounts