

[See all 67 Products in Family](#)

LightPath 354240 | 1064nm Alignment, 0.50 NA Fiber Collimator w/ SMA Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock #64-782 **8 In Stock**

⊖ 1 ⊕ **S\$371⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-10	S\$371.00 each
Qty 11-25	S\$327.60 each
Qty 26-49	S\$309.40 each
Need More?	Request Quote

Product Downloads

General

354240 **Lightpath Lens Code:**
Fiber Collimator **Type:**

#37-104

Lens Included:

Physical & Mechanical Properties

8.00 **Clear Aperture CA (mm):**
Bevel:
Protective as needed

304L Stainless Steel Housing **Construction:**

12.00 **Housing Diameter (mm):**

12.7 **Housing Length (mm):**

Optical Properties

8.00 @ 780nm **Effective Focal Length EFL (mm):**

0.50 **Numerical Aperture NA:**

Substrate:
ECO-550

BBAR (1050-1600nm) **Coating:**

Coating Specification:
R_{abs} <1.0% @ 1050 - 1600nm

40-20 **Surface Quality:**

1.00 **f#:**

50.02 **Abbe Number (v_d):**

1.606 **Index of Refraction (n_d):**

1050 - 1600 **Wavelength Range (nm):**

Infinite **Conjugate Distance:**

780.00 **Focal Length Specification Wavelength (nm):**

1064 **Alignment Wavelength (nm):**

<0.080 **Transmitted Wavefront Error (λ, RMS):**

Hardware & Interface Connectivity

SMA **Connector:**

Threading & Mounting

M12 x0.5 **Mount:**

Material Properties

11.1 **Coefficient of Thermal Expansion CTE (10⁻⁶/°C):**

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 247:
Compliant

Product Details

- Easy to Integrate
- Models for FC/PC, FC/APC, and SMA Connections Available
- Four Wavelength Ranges Covering 350-1600nm

LightPath® Fiber Optic Collimators are designed to collimate light exiting a fiber to a desired beam diameter or spot size or to focus light into a fiber when used in reverse. The lenses are diffraction limited, so they can achieve spot sizes down to a few microns. Lenses also feature an antireflection coating for low back reflection. LightPath® Fiber Optic Collimators are designed so that they can be used in pairs to couple the input and output light of optical devices. Optimum performance for long-term use is ensured by the factory set and tested lens alignment. Typical applications can include use with fiber coupled lasers and pigtailed receptacles, as well as communications and data transfer.

Technical Information

