


[See all 32 Products in Family](#)

# 1070nm, 18-23mm Dia. Input Beam, HP Sapphire Focal Flat Top Beam Shaper | Focal $\pi$ Shaper\_1070\_Q-20\_HP

See More by [AdiOptica](#)



Stock #17-594 [CONTACT US](#)

⊖ 1 ⊕ \$6,111<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	\$6,111.00 each
Qty 5-10	\$5,494.00 each
Qty 11+	\$5,192.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

$\pi$ Shaper\_1070\_Q-20\_HP **Model Number:**

Beam Shaper (Sapphire) **Type:**

[#12-322](#) Compatible Adapter:

### Physical & Mechanical Properties

21.00 Length (mm):

70 Weight (g):

38 Clear Aperture CA (mm):

64.00 Diameter (mm):

18 - 23 Input Beam Diameter,  $1/e^2$  (mm):

### Optical Properties

>99 Transmission (%):

1070 Design Wavelength DWL (nm):

1020 - 1100 Wavelength Range (nm):

TEM<sub>00</sub> Input Beam Mode:

<1.5 Typical Input Beam Mode Quality, M<sup>2</sup>:

±20 Input Beam Divergence (mrad):

### Electrical

5 Maximum Input Power, CW (kW):

### Threading & Mounting

M58 x 1 Inner Thread:

M58 x 1 Outer Thread:

### Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 250:

## Product Details

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica πShaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal-πShaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal-πShapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

## Technical Information

