

[See all 36 Products in Family](#)

## 10mm Dia., 1.5mm Thick, BBAR (1650-3000nm) Coated, Suprasil Window



Suprasil® Windows

Stock #21-242 **5 In Stock**

⊖ 1 ⊕ **S\$212<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>S\$212.80</b> each
Qty 6-25	<b>S\$169.40</b> each
Qty 26-49	<b>S\$159.60</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Protective Window **Type:**

### Physical & Mechanical Properties

Protective as needed **Bevel:**

90 **Clear Aperture (%):**

9.00	Clear Aperture CA (mm):
10.00 +0.00/-0.10	Diameter (mm):
1.50 ±0.10	Thickness (mm):
Fine Ground	Edges:
591.00	Knoop Hardness (kg/mm <sup>2</sup> ):
<5	Parallelism (arcsec):
0.17	Poisson's Ratio:
70	Young's Modulus (GPa):

## Optical Properties

67.8	Abbe Number (v <sub>d</sub> ):
BBAR (1650-3000nm)	Coating:
R <sub>avg</sub> <1% @ 1650 - 3000nm R <sub>abs</sub> <2% @ 1650 - 3000nm	Coating Specification:
1.459	Index of Refraction (n <sub>d</sub> ):
Suprasil® 300	Substrate:
10-5	Surface Quality:
λ/10	Transmitted Wavefront, P-V:
1650 - 3000	Wavelength Range (nm):

## Material Properties

0.51 (0 to +100°C) 0.58 (0 to +200°C)	Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C):
2.20	Density (g/cm <sup>3</sup> ):

## Regulatory Compliance


<a href="#">Compliant</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	Reach 235:

## Product Details

- High Transmission from 200 to 3500nm
- <1 ppm OH Content for Minimal Absorption Losses
- 10-5 Surface Quality and up to λ/10 TWD

Suprasil® Windows are constructed from high purity synthetic fused silica and provide high, flat transmission from 200 to 3500nm. Suprasil has similar mechanical properties to fused silica with the added benefit of having no absorption bands in the visible or infrared spectra, resulting in no transmission loss between 1400 - 2700nm. Compared to Infrasil®, Suprasil has lower absorption with a <1 ppm OH content, causing negligible increase in temperature from bulk absorption when used with high powered lasers. Suprasil Windows are ideal for laser material processing, medical laser applications, or applications using Nd:doped or 2 micron lasers.

## Technical Information



## Compatible Mounts

---