

TECHSPEC® 1.0X SilverTL™ Telecentric Lens



1.0X Magnification



Stock **#58-430** [CONTACT US](#)

-

1

+

S\$788^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	S\$788.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Series:

SilverTL™ Series

Stock No. of Mounting Clamp:

#56-870 Sold Separately

Telecentric LensType:

Physical & Mechanical Properties

VariableIris Option:

114.00Length (mm):

114.00Length excluding Threads (mm):

40.00Maximum Diameter (mm):

193Weight (g):

Anodized AluminumConstruction:

Optical Properties

8.8mmHorizontal Field of View, 2/3" Sensor:

6.4mmHorizontal Field of View, 1/2" Sensor:

4.8mmHorizontal Field of View, 1/3" Sensor:

11.00Maximum Image Circle (mm):

0.082Numerical Aperture NA, Object Side:

±3Working Distance Tolerance (mm):

>40% @ 40 lp/mmResolution, Image Space MTF @ f/10:

6 (5)Number of Elements (Groups):

<0.045Typical Telecentricity @ 588nm (°):

<0.060Typical Distortion @ 588nm (%):

1XPrimary Magnification PMAG:

1.00Telecentric Lens Magnification:

83.00Working Distance (mm):

8.8 x 6.6FOV @ Max Sensor Format, H x V (mm):

f/6 - f/22Aperture (f/#):

425 - 675nm BBARCoating:

±0.5 at f/10 (20% @ 20 lp/mm)Depth of Field (mm):

1XMagnification:

VSLens Wavelength Range:

Sensor

2/3"Maximum Sensor Format:

2.74Pixel Size (µm):

Threading & Mounting

M37 x 0.75 (Female)Filter Thread:

C-MountMount:

Regulatory Compliance

CompliantRoHS 2015:

Certificate of Conformance:


PRODUCT DETAILS

- High Resolution f/6 Bi-Telecentric Lens with Inline Illumination Options
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Up to 2/3", C-Mount Telecentric Lens
- Magnification from 0.16X to 4X


TECHSPEC® SilverTL™ Telecentric Lenses are ideal for both on-line and off-line machine vision production applications that require accurate measurements. These lenses combine high-quality optics with a simplified non-focusing mechanical design and an adjustable iris with a locking set screw. These lenses are designed for metrology and gauging applications. TECHSPEC® SilverTL™ Telecentric Lenses also offer inline illumination options for maximum versatility. Each lens also features a standard front filter thread for use with [color filters](#), [polarizers](#), [protective windows](#), and [illumination adapters](#) for LED or fiber-optic ring lights.

Note: Mounting brackets are available that fit the 30mm diameter mounting surface.


TECHNICAL INFORMATION




#58-430, 1.0X SilverTL™ Telecentric Lens, Distortion Plot



#58-430, 1.0X SilverTL™ Telecentric Lens, Relative Illumination Plot




#58-430, 1.0X SilverTL™ Telecentric Lens, Telecentricity Plot




#58-430, 1.0X SilverTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 83mm Working Distance, f6



#58-430, 1.0X SilverTL™ Telecentric Lens, Depth of Field Plot, 83mm Working Distance, f6





#58-430, 1.0X SilverTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 83mm Working Distance, f10



#58-430, 1.0X SilverTL™ Telecentric Lens, Depth of Field Plot, 83mm Working Distance, f10

Stock Number	Primary Mag.	Max Diameter A	Mounting Diameter B	Length C	Mounting Length D	Mounting Offset E	Filter Thread F
#56-675	0.16X	65mm	30mm	191mm	50mm	43mm	M62 x0.75

#63-073	0.20X	60mm	30mm	188mm	42mm	45mm	M58 x 0.75
#56-676	0.25X	48mm	30mm	158mm	49mm	44mm	M46 x 0.75
#58-428	0.30X	46mm	30mm	158mm	60mm	43mm	M43 x 0.75
#56-677	0.40X	45mm	30mm	159mm	67mm	33mm	M43 x 0.75
#63-074	0.50X	40mm	30mm	153mm	42mm	68mm	M37 x 0.75
#88-344 (In-Line)				156.2mm	45.1mm	73.4mm	
#56-678	0.60X	42mm	30mm	156mm	57mm	46mm	M40.5 x 0.5
#67-731	0.75X	36mm	30mm	151.2mm	34mm*	82.2mm	M30.5 x 0.5
#88-346 (In-Line)				155.2mm	46.2mm	16.9mm	
#58-430	1.0X	40mm	30mm	114mm	32mm*	17mm	M37 x 0.75
#58-431	2.0X	45mm	30mm	141mm	45mm	17mm	M43 x 0.75
#88-348 (In-Line)				144.6mm	42.2mm	18.8mm	
#58-432	4.0X	61mm	30mm	249mm	99mm	17mm	M58 x 0.75



*Mounting clamp fits over iris