

## 120 MHz Fiber Coupled Optical Receiver Module



Stock #87-324 CLEARANCE **5 In Stock**

S\$261<sup>00</sup>

ADD TO CART

Volume Pricing	
Qty 1+	S\$261.80 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Optical Properties

1310 - 1550      **Wavelength Range (nm):**

50/125/245/900      **Fiber Diameter (µm):**

### Sensor

25.00      **Dynamic Range (dB):**

### Electrical

**Sensitivity (dBm):**

**Hardware & Interface Connectivity**

FC/PC Connector: **Connector:**

**Regulatory Compliance**


[View](#) Certificate of Conformance:

**Product Details**

- High Sensitivity and Overload Power with Wide Dynamic Range
- Designed for Bandwidths of 3MHz and 120MHz and Wavelength Ranges of 1310 – 1550nm
- Ideal for Biomedical, Industrial, or Telecommunication Optical Sensor Systems

Fiber-Coupled Optical Receiver Modules are ideal for use in biomedical optical sensor systems or for industrial and telecommunication sensing applications. Fiber-Coupled Optical Receiver Modules feature high sensitivity and high overload power, in addition to wide dynamic ranges. These receiver modules are designed for use in common telecommunication wavelength ranges.

**Technical Information**



Pin	Function
1	-5V detector bias
2, 6, 9, 11	No connection
12, 13, 14	No connection
3, 5, 8	Ground
4	-5V (LDFR = NC)
7	Output
10	+5V