

# 12.5 x 12.5mm Ultra Broadband Wire Grid Linear Polarizer



Unmounted Ultra Broadband Wire Grid Linear Polarizer

Stock **#68-749** **5 In Stock**

-

1

+

S\$1,477<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | S\$1,477.00 each              |
| Qty 11+        | S\$1,260.00 each              |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Linear Polarizer

Type:

Physical & Mechanical Properties

8.5 x 8.5

Clear Aperture CA (mm):

12.50

Length (mm):

Dimensions (mm):

|             |                             |
|-------------|-----------------------------|
| 12.5 x 12.5 |                             |
| 2.13 ±0.2   | Thickness (mm):             |
|             |                             |
| ±0.4        | Dimensional Tolerance (mm): |
|             |                             |
| Wire Grid   | Construction:               |
|             |                             |
| ±1.0        | Alignment Tolerance (°):    |
|             |                             |
| 12.50       | Width (mm):                 |

### Optical Properties

|                                             |                                     |
|---------------------------------------------|-------------------------------------|
| ±20 without depolarization                  | Angle of Incidence (°):             |
|                                             |                                     |
| 5000:1 @ 3200nm                             | Extinction Ratio:                   |
|                                             |                                     |
| <a href="#">Fused Silica</a> (Corning 7980) | Substrate: <input type="checkbox"/> |
|                                             |                                     |
| 80-50                                       | Surface Quality:                    |
|                                             |                                     |
| >80 (Typical) @ 450nm                       | Transmission (%):                   |
|                                             |                                     |
| 300 - 3200                                  | Wavelength Range (nm):              |

### Material Properties

|                            |                    |
|----------------------------|--------------------|
| 5.5 x 10 <sup>-7</sup> /°C | Thermal Expansion: |
|----------------------------|--------------------|

### Environmental & Durability Factors

|             |                             |
|-------------|-----------------------------|
| -40 to +200 | Operating Temperature (°C): |
|-------------|-----------------------------|

### Regulatory Compliance

|                           |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
|                           |                             |
| <a href="#">Compliant</a> | Reach 224:                  |
|                           |                             |
| <a href="#">View</a>      | Certificate of Conformance: |

## Product Details

- Reflect S-Polarized Light
- Transmit P-Polarized Light
- Excellent Performance from UV to IR

Ultra Broadband Wire Grid Polarizers consist of a thin layer of aluminum MicroWires layered between two Fused Silica windows. Designed for multi-wavelength applications, these polarizers have excellent heat resistance and performance beginning in the UV and extending into the infrared (IR). The polarizers feature a fused silica substrate. Ultra Broadband Wire Grid Polarizers reflect S-polarized light and transmit P-polarized light. These polarizers are available in a variety of thicknesses and clear apertures, in either a 12.5, 25, or 50mm diameter.

**Note:** The input beam should be oriented towards the cover glass side, indicated by a reference mark which also indicates the direction of the transmission axis.

Wire Grid Polarizers are constructed by attaching MicroWires to the first window, and then applying a thin cover glass onto the wire grid surface to protect the wire from damage. The light is polarized by the birefringent nature of the wire grid surface. When incident light strikes the wire grid, P-polarized light contacts a dielectric and is transmitted, while S-polarized light contacts a mirror and is reflected.

## Technical Information

