

TECHSPEC[®] 12.5mm 532nm, Laser Line Non-Polarizing Cube Beamsplitter



Laser Line Non-Polarizing Cube Beamsplitters



Stock **#35-959** 4 In Stock

-

1

+

S\$401^{.80}

ADD TO CART

Volume Pricing	
Qty 1-5	S\$401.80 each
Qty 6-25	S\$322.00 each
Qty 26-99	S\$295.40 each
Need More?	Request Quote

Product Downloads

General

Non-Polarizing Beamsplitter

Type:

Physical & Mechanical Properties

Protective as needed

Bevel:

90	Clear Aperture (%):
Cube	Construction:
12.5 x 12.5 x 12.5 ±0.1	Dimensions (mm):

Optical Properties	
±2	Beam Deviation (arcmin):
Coating Specification: <0.25% Reflection on Entrance and Exit Faces	
532	Design Wavelength DWL (nm):
±5	Reflection/Transmission Tolerance (%):
N-BK7	Substrate: ☐
40-20	Surface Quality:
Transmission (%): <45% ±5% @ DWL	
Ts-Tp : <3% @ DWL	
1.50	Power (fringes) @ 632.8nm:
0.25	Irregularity (fringes) @ 632.8nm:

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:

Product Details

• <3% Transmission Difference for S and P Polarization States

• AR Coated <0.25% on Entrance and Exit Faces

• Nd:YAG and HeNe Options

TECHSPEC® Laser Line Non-Polarizing Cube Beamsplitters offer users the ability to split light evenly into orthogonal paths regardless of the incoming polarization state. These cubes are designed with a metallic-dielectric hybrid coating that yields less than a 3% difference in transmission for S-polarized and P-polarized light. These cubes are compatible with common Nd:YAG and HeNe lasers and are available with three beamsplitter coating options at 1064nm, 632nm, and 532nm. Efficiency is enhanced with AR coatings on the entrance and exit faces featuring <0.25% reflection per surface. TECHSPEC® Laser Line Non-Polarizing Cube Beamsplitters will displace a beam by less than 2 arcmin, making them easy to integrate into alignment sensitive applications.



Technical Information



