

TECHSPEC<sup>®</sup> 12.5mm Dia. Uncoated,  $\lambda/10$  Fused Silica Window



TECHSPEC<sup>®</sup> Uncoated Laser Window Substrates

Stock **#48-022** 20+ In Stock

-

1

+

S\$186<sup>09</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | <b>S\$186.69</b> each         |
| Qty 6-25       | <b>S\$164.29</b> each         |
| Qty 26-49      | <b>S\$149.35</b> each         |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

SPECIFICATIONS

General

Laser Line Window

Type:

Type of Window:

|                                  |                                                                      |
|----------------------------------|----------------------------------------------------------------------|
| Glass                            |                                                                      |
| Physical & Mechanical Properties |                                                                      |
| 11.25                            | Clear Aperture CA (mm):                                              |
| 12.50 +0.00/-0.10                | Diameter (mm):                                                       |
| 3.00 ±0.10                       | Thickness (mm):                                                      |
| Protective as needed             | Bevel:                                                               |
| 90                               | Clear Aperture (%):                                                  |
| ≤5                               | Parallelism (arcsec):                                                |
| Fine Ground                      | Edges:                                                               |
| Optical Properties               |                                                                      |
| 0                                | Angle of Incidence (°):                                              |
| Uncoated                         | Coating:                                                             |
| <a href="#">Fused Silica</a>     | Substrate: <input type="checkbox"/> Excimer Grade (Corning 7980 KrF) |
| 1.458                            | Index of Refraction (n <sub>d</sub> ):                               |
| 10-5                             | Surface Quality:                                                     |
| λ/10                             | Transmitted Wavefront, P-V:                                          |
| 67.8                             | Abbe Number (v <sub>d</sub> ):                                       |
| 200 - 2200                       | Wavelength Range (nm):                                               |
| Material Properties              |                                                                      |
| 7980 KrF 0A                      | Fused Silica Grade:                                                  |
| Regulatory Compliance            |                                                                      |
| <a href="#">Compliant</a>        | RoHS 2015:                                                           |
| <a href="#">Compliant</a>        | REACH 201:                                                           |
| <a href="#">View</a>             | Certificate of Conformance:                                          |

## PRODUCT DETAILS

- Up to 10-5 Surface Quality and λ/10 Surface Flatness Available
- Fused Silica or N-BK7 Material
- Standard Imperial Sizes for Drop-in Replacement Solutions
- [Laser Line Coated Versions](#) Available
- [Mirror Substrates](#) Also Available

TECHSPEC® Uncoated Laser Window Substrates are laser quality window substrates designed to be used in demanding laser applications. These laser window substrates are available, manufactured from fused silica for high power laser applications that require excellent thermal stability or from N-BK7 for more cost sensitive laser applications. Both the fused silica and N-BK7 laser window substrates feature precision grade λ/10 surface flatness and 10-5 surface quality, ensuring minimal disturbance to transmitted beams. TECHSPEC® Uncoated Laser Window Substrates are available in standard imperial sizes from 12.7 to 50.8mm in diameter for the convenience of drop-in replacement into existing laser systems. Custom dimensional and coating options are available, please contact us for custom inquiries.

## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## COMPATIBLE MOUNTS

