

TECHSPEC[®] 12.5mm Diameter, 850nm Cut-On SWIR Longpass Filter



Stock **#86-449** 20+ In Stock

-

1

+

S\$99^{.40}

ADD TO CART

Volume Pricing	
Qty 1-9	S\$99.40 each
Qty 10-25	S\$89.60 each
Qty 26-49	S\$85.40 each
Need More?	Request Quote

Product Downloads

General	
Longpass Filter	Type:
Physical & Mechanical Properties	
12.50	Diameter (mm):
1.20 ±0.15	Thickness (mm):

Dimensional Tolerance (mm):	
+0.0/-0.2	
Optical Properties	
Cut-On Wavelength (nm):	
850.00	
Substrate: □	
BOROFLOAT®	
Coating:	
Traditional Coated	
Rejection Wavelength (nm):	
350 - 835	
Surface Quality:	
80-50	
Transmission Wavelength (nm):	
880 - 2500	
Cut-On Wavelength (µm):	
0.85	
Coating Specification:	
T _{avg} <0.5% @ 350 - 835nm	
T _{avg} >85% @ 880 - 1700 nm	
T _{avg} >75% @ 1700 - 2500nm	
Wavelength Range (nm):	
350 - 2500	
Surface Flatness (P-V):	
4 - 6λ	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
REACH 241:	
Compliant	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Block Visible Wavelengths
- Ideal for Machine Vision Applications
- Can Be Used as Cold Mirrors
- Additional [Longpass Edge Filters](#) Available

Designed to pass short-wave infrared (SWIR) wavelengths while blocking visible light, TECHSPEC® SWIR Longpass Filters are ideal for increasing the image quality of InGaAs cameras in a variety of machine vision applications. These longpass edge filters are offered in multiple sizes and cut-on wavelengths. TECHSPEC SWIR Longpass Filters can also be used as extended cold mirrors to eliminate damage or adverse effects caused by heat build-up.

Technical Information



Compatible Mounts

