

TECHSPEC®

S-Mount, 12.5mm x 17.6mm Plate Mount



Plate S-Mount Holder (#11-142)

Stock **#11-142** 2 In Stock

-

1

+

S\$389²⁰

ADD TO CART

Volume Pricing	
Qty 1-4	S\$389.20 each
Qty 5-9	S\$364.00 each
Qty 10-25	S\$346.36 each
Need More?	Request Quote

Product Downloads

General

Function:	
Optic Mount (Fixed)	
Type of Optics:	
Rectangular	
Note:	
Includes one S-Mount Aperture Cap (# 11-137)	
Dimensions of Compatible Optics (mm):	
12.5 x 17.6	

Physical & Mechanical Properties

30.0 x 30.0 x 28.5 **Dimensions (mm):**

30.0 **Extension Length (mm):**

Min. Thickness of Compatible Optics (mm):

Material	Thickness (mm)
1.0	

3.0	Max. Thickness of Compatible Optics (mm):
-----	---

Threading & Mounting

Thread Type:

Compatible Post:

Threading & Mounting

Thread Type: S-Mount

14-20 **Compatible Post:**

Regulatory Compliance

Regulatory Compliance

Compliant	RoHS 2015:
-----------	------------

[View](#) Certificate of Conformance:

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: [#11-139](#) and [#11-142](#) each include one S-Mount Aperture Cap ([#11-137](#))

Technical Information

