

**TECHSPEC® 12.7mm Dia., 266nm T, 532 & 1064nm R 45° Harmonic Separator**



TECHSPEC Nd:YAG Harmonic Separators

Stock #11-547 **13 In Stock**

⊖ 1 ⊕ **S\$411<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>S\$411.60</b> each
Qty 6-24	<b>S\$369.60</b> each
Qty 25-49	<b>S\$329.00</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Harmonic Beamsplitter **Type:**

**Physical & Mechanical Properties**

>90 **Clear Aperture (%):**

Dichroic **Construction:**

12.70 +0.00/-0.10 **Diameter (mm):**

<3 **Parallelism (arcmin):**

6.35 ±0.20 **Thickness (mm):**

## Optical Properties

45 **Angle of Incidence (°):**

**Coating Specification:**  
Surface 1: R<sub>abs</sub>: >99% @ 532nm, R<sub>abs</sub>: >99% @ 1064nm, T<sub>abs</sub>: >70% @ 266nm  
Surface 2: R<sub>abs</sub>: <1.0% @ 266nm

532, 1064 **Reflection Wavelength (nm):**

**Substrate:**   
[Fused Silica](#) (Corning 7980)

M10 **Surface Flatness (P-V):**

10-5 **Surface Quality:**

266 **Transmission Wavelength (nm):**

**Damage Threshold, By Design:**   
Surface 1:  
1 J/cm<sup>2</sup> @ 266nm, 20ns, 20Hz  
5 J/cm<sup>2</sup> @ 532nm, 20ns, 20Hz  
7.5 J/cm<sup>2</sup> @ 1064nm, 20ns, 20Hz  
Surface 2:  
1 J/cm<sup>2</sup> @ 20ns, 20Hz @ 266nm

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Used to Separate Nd:YAG Harmonic Wavelengths
- Beamsplitter Coating Features >95% Transmission
- M10 Fused Silica Substrate

TECHSPEC® Nd:YAG Harmonic Separators are used to separate the common harmonic wavelengths of an Nd:YAG laser. A beamsplitter coating on the first surface reflects at least one wavelength and transmits another. The second surface of the beamsplitter features an anti-reflective coating to minimize the loss due to reflection. TECHSPEC Nd:YAG Harmonic Separators are available in 45° and 0° angle of incidence options. These harmonic separators are available in multiple wavelength configurations for optimal flexibility in system design.

**Note:** The Damage Threshold values we publish for this family of products were all tested independently from one another. When using these products with more than 1 incident beam, the resulting Damage Threshold of the system will be negatively impacted.

## Compatible Mounts