

[See all 3 Products in Family](#)

12.7mm Dia. 300 - 2700nm Broadband Polarizer



Broadband Polarizers

Stock **#71-207** **1 In Stock**

S\$1,190⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,190.00 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

10.16 **Clear Aperture CA (mm):**

12.70 **Diameter (mm):**

2.50 ±0.3 **Thickness (mm):**

Dimensional Tolerance (mm):

+0.0/-0.1

Optical Properties**Angle of Incidence (°):**

±40

Extinction Ratio:

>100:1 @ 300 - 400nm (Typical)
 >50,000:1 @ 450 - 550nm (Typical)
 >800:1 @ 700 - 1400nm (Typical)
 >1000:1 @ 1400 - 2650nm (Typical)

Substrate:

Fused Silica (Corning 7980)

Wavelength Range (nm):

300 - 2700

Polarization Axis Mark (°):

±2

Threading & Mounting**Mount Thickness (mm):**

4.5

Environmental & Durability Factors**Operating Temperature (°C):**

-50 to 80

Regulatory Compliance**Certificate of Conformance:**[View](#)**Product Details**

- Wide Acceptance Angles
- Broadband Performance from 300 -2700nm
- Compact Designs Ease System Integration

Broadband Polarizers are ideal solutions for broadband applications from the UV to SWIR where wire grid polarizers are not practical. Broadband Polarizers feature acceptance angles of ±40° and are well suited for use with uncollimated light sources. Additionally, these polarizers utilize a proprietary design that allows for consistent transmitted contrast from 300 – 2700nm.

Note: The input beam should enter through the front of the optic, which is the engraved side.

Technical Information