

TECHSPEC® 12.7mm Dia., 532nm T, 1064nm R 45° Thin Harmonic Separator



TECHSPEC Nd:YAG Harmonic Separators

Stock #29-054 **14 In Stock**

⊖ 1 ⊕ **\$411⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-5	\$411.60 each
Qty 6-24	\$369.60 each
Qty 25-49	\$329.00 each
Need More?	Request Quote

Product Downloads

General

Laser Window Substrate **Type:**

Physical & Mechanical Properties

90 **Clear Aperture (%):**

Dichroic **Construction:**

12.70 +0.00/-0.10 **Diameter (mm):**

<3 **Parallelism (arcmin):**

3.18 ± 0.20 **Thickness (mm):**

Optical Properties

45 **Angle of Incidence (°):**

Coating Specification:
Surface 1: R_{abs}: >99% @ 1064nm, T_{abs}: >95% @ 532nm
Surface 2: R_{abs}: <0.5% @ 532nm

1064 **Reflection Wavelength (nm):**

Substrate:
[Fused Silica](#) (Corning 7980)

λ/10 **Surface Flatness (P-V):**

10-5 **Surface Quality:**

532 **Transmission Wavelength (nm):**

Damage Threshold, By Design:
Surface 1:
7.5 J/cm² @ 1064nm, 20ns, 20Hz
7.5 J/cm² @ 532nm, 20ns, 20Hz
Surface 2:
10 J/cm² @ 532nm, 20ns, 20Hz

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Used to Separate Nd:YAG Harmonic Wavelengths
- Beamsplitter Coating Features >95% Transmission
- λ/10 Fused Silica Substrate

TECHSPEC® Nd:YAG Harmonic Separators are used to separate the common harmonic wavelengths of an Nd:YAG laser. A beamsplitter coating on the first surface reflects at least one wavelength and transmits another. The second surface of the beamsplitter features an anti-reflective coating to minimize the loss due to reflection. TECHSPEC Nd:YAG Harmonic Separators are available in 45° and 0° angle of incidence options. These harmonic separators are available in multiple wavelength configurations for optimal flexibility in system design.

Note: The Damage Threshold values we publish for this family of products were all tested independently from one another. When using these products with more than 1 incident beam, the resulting Damage Threshold of the system will be negatively impacted.