

TECHSPEC<sup>®</sup> 12.7mm Dia., 680 - 1020nm, 70R:30T, Ultrafast Beamsplitter



TECHSPEC<sup>®</sup> Ultrafast Beamsplitters

Stock **#13-831** 20+ In Stock

-

1

+

S\$350<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | S\$350.00 each                |
| Qty 5-9        | S\$310.80 each                |
| Qty 10-19      | S\$274.40 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                               |                 |
|---------------------------------------|-----------------|
| Ultrafast Non-Polarizing Beamsplitter | Type:           |
| Physical & Mechanical Properties      |                 |
| 3.00 ±0.10                            | Thickness (mm): |
| 12.70 +0.00/-0.10                     | Diameter (mm):  |

|                                                                                                                                                                                                                                                             |                                      |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------|
| 80                                                                                                                                                                                                                                                          | Clear Aperture (%):                  |
| <10                                                                                                                                                                                                                                                         | Parallelism (arcsec):                |
| Optical Properties                                                                                                                                                                                                                                          |                                      |
| Fused Silica (Corning 7980)                                                                                                                                                                                                                                 | Substrate: <input type="checkbox"/>  |
| 10-5                                                                                                                                                                                                                                                        | Surface Quality:                     |
| 45                                                                                                                                                                                                                                                          | Angle of Incidence (°):              |
| 680 - 1020                                                                                                                                                                                                                                                  | Wavelength Range (nm):               |
| 70/30                                                                                                                                                                                                                                                       | Reflection/Transmission Ratio (R/T): |
| Coating Specification:<br>Surface 1:<br>R <sub>avg</sub> = 70±3% @ 680 - 1020nm<br>R <sub>p</sub> = 56±3% @ 680 - 1020nm<br>R <sub>s</sub> = 85±3% @ 680 - 1020nm<br>Surface 2:<br>R <sub>s</sub> <2% @ 650 - 1100nm<br>R <sub>p</sub> <1.5% @ 650 - 1100nm |                                      |
| GDD Specification:<br>Transmission: ±15 fs <sup>2</sup> @ 700 - 1080nm<br>Reflectivity: ±20 fs <sup>2</sup> @ 700 - 1080nm                                                                                                                                  |                                      |
| λ/8 @ 632.8nm                                                                                                                                                                                                                                               | Transmitted Wavefront Distortion:    |
| <λ/6 @ 632.8nm                                                                                                                                                                                                                                              | Reflected Wavefront Distortion:      |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| View                  | Certificate of Conformance: |


## Product Details

- Designs for Ti:sapphire and Yb:doped Fiber Lasers
- 90:10, 70:30, and 50:50 (R:T) Split Ratios
- Controlled Reflection and Transmission GDD

TECHSPEC® Ultrafast Beamsplitters are designed for use with femtosecond pulsed Ti:sapphire and Yb:doped fiber lasers. Their front surface features a 90:10, 70:30, or 50:50 (R:T) non-polarizing beamsplitter coating while their back surface features an anti-reflective coating to minimize losses due to reflection. Each coating has controlled dispersion to allow for predictable group delay dispersion (GDD) of the transmitted or reflected pulses. TECHSPEC Ultrafast Beamsplitters are available in standard imperial sizes for easy integration into optical systems. Please [contact us](#) if your application requires an Ultrafast Beamsplitter with a custom size or coating specifications.

**Note:** The arrow on the edge of these optics points towards the beamsplitter coating.

## Technical Information



## Compatible Mounts