


[See all 1 Products in Family](#)

12.7mm Dia., Protected Gold Coated, ISP Optics $\lambda/4$ Mirror | P-MF-AU-12

See More by [ISP Optics](#)



Stock #25-011 CLEARANCE **7 In Stock**

⊖ 1 ⊕ **S\$144²⁰**

ADD TO CART

Volume Pricing	
Qty 1+	S\$144.20 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror **Type:**
P-MF-AU-12 **Model Number:**

Physical & Mechanical Properties

12.70 +0.00/-0.13 **Diameter (mm):**
6.35 ±0.20 **Thickness (mm):**

Fine Grind **Back Surface:**

11.43 **Clear Aperture CA (mm):**

Fine Ground **Edges:**

Optical Properties

Metal **Coating Type:**

Protected Gold (3000-5000nm) **Coating:**

$\lambda/4$ **Surface Flatness (P-V):**

3000 - 5000 **Wavelength Range (nm):**

Pyrex **Substrate:**

$R_{avg} \geq 95\%$ @ 3000 - 5000nm **Coating Specification:**

40-20 **Surface Quality:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Pyrex® Mirror Substrates
- Protected Gold Coating
- Ideal for LWMR Applications

ISP Optics Gold Coated Mirrors feature a protected gold coating on a Pyrex® mirror substrate with an operating wavelength range of 0.7 – 12µm. Protected gold is the most efficient reflective coating over the entire Infrared (IR) wavelength range. In addition, Pyrex® is a low-expansion material, making it relatively insensitive to temperature changes. As such, ISP Optics Gold Coated Mirrors are ideal for a wide range of IR applications. A protective dielectric overcoat is deposited over the gold to protect the fragile coating from damage and to make cleaning and handling easier.