

[See all 51 Products in Family](#)

**TECHSPEC® 12.7mm Dia. x 35mm FL, 3-12µm BBAR Coated, ZnSe Plano-Convex Lens**

See More by [Coherent®](#)



TECHSPEC Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

Stock **#11-421** **10 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ **\$628<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-10	<b>\$628.60</b> each
Qty 11-25	<b>\$565.60</b> each
Qty 26-49	<b>\$443.80</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Plano-Convex Lens **Type:**

**Physical & Mechanical Properties**

12.70 +0.00/-0.10 **Diameter (mm):**

≤50.8	<b>Centering, ETD (μm):</b>
2.50 ±0.10	<b>Center Thickness CT (mm):</b>
2.09	<b>Edge Thickness ET (mm):</b>
11.43	<b>Clear Aperture CA (mm):</b>
Protective as needed	<b>Bevel:</b>
<50 RMS	<b>Surface Roughness (□):</b>

## Optical Properties

35.00 @ 10.6μm	<b>Effective Focal Length EFL (mm):</b>
33.96	<b>Back Focal Length BFL (mm):</b>
BBAR (3000-12000nm)	<b>Coating:</b>
R <sub>avg</sub> ≤3.0% @ 3 - 12μm	<b>Coating Specification:</b>
Coherent® Infrared ZnSe	<b>Substrate:</b> □
40-20	<b>Surface Quality:</b>
λ	<b>Power (P-V) @ 632.8nm:</b>
λ/20	<b>Irregularity (P-V) @ 10.6μm:</b>
49.10	<b>Radius R<sub>1</sub> (mm):</b>
2.76	<b>f/#:</b>
0.18	<b>Numerical Aperture NA:</b>
3000 - 12000	<b>Wavelength Range (nm):</b>
<0.0005 @ 10.6μm	<b>Bulk Absorption Coefficient (cm<sup>-1</sup>):</b>

## Electrical

λ/10	<b>Power (P-V) @ 10.6μm:</b>
------	------------------------------

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 242:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Edmund Optics® Designed, Coherent® Manufactured
- Premier Grade ZnSe Material
- Uncoated or Broadband AR Coating Options

TECHSPEC® Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses are designed for focusing or collimation applications in the mid-wave and longwave infrared spectrum. Manufactured by Coherent®, these lenses feature Infrared ZnSe material with <0.0005cm<sup>-1</sup> bulk absorption at 10.6μm and are available uncoated or with a variety of broadband anti-reflection coating options. The 8-12μm coating is ideal for use with CO<sub>2</sub> lasers and thermal camera applications, whereas the dual band 3-12μm coating is ideal for hyperspectral applications. TECHSPEC® Zinc Selenide PCX Lenses feature an irregularity of <λ/20 at 10.6μm, 40-20 surface quality, and <50Å surface roughness. Three diameter options are available, with effective focal lengths ranging from 12.7mm to 250mm.

**Notes:** II-VI Incorporated is now Coherent Corp.

## Technical Information



**AR COATED ZINC SELENIDE**

**ZnSe with 3-12 $\mu\text{m}$  AR Coating  
Typical Transmission**

Wavelength $\lambda$ ( $\mu\text{m}$ )	Transmission T (%)
2	70
3	95
4	97
5	95
6	97
7	96
8	95
9	96
10	96
11	96
12	95
13	92
14	85

Typical transmission of a ZnSe window with BBAR (3000-12000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{\text{avg}} < 5.0\%$  @ 3 - 12 $\mu\text{m}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

---

**ZnSe with 8-12 $\mu\text{m}$  AR Coating  
Typical Transmission**

Wavelength $\lambda$ ( $\mu\text{m}$ )	Transmission T (%)
6	70
7	90
8	98
9	99
10	99
11	98
12	95
13	90
14	85

Typical transmission of a ZnSe window with BBAR (8000-12000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{\text{avg}} \leq 0.5\%$  @ 8 - 12 $\mu\text{m}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

## Compatible Mounts

---